

Suite 600 - 2889 E 12th Ave Vancouver, BC V5M 4T5

Toll Free: 1-866-566-7233 www.technicalsafetybc.ca

TECHNICAL STANDARDS & SAFETY AUTHORITY 345 CARLINGVIEW DRIVE TORONTO ON M9W 6N9

Date: November 18, 2020

Account #: 35231 **Journal #:** 76885

Attn: TSSA

Re: Application for Design Registration

The design, as detailed in your, 0D22748.5, for a Fitting is accepted for registration as follows:

Registered To: SWAGELOK COMPANY CRN: 0D22748.51

Drawing #: Scope of Registration **Drawing Revision:** N/A

Conditions Of Registration:

This design was registered based on a technical review performed by the province of initial registration in accordance with the Association of Chief Inspectors policy on reciprocal recognition of design review.

Scope of Registration: Crimped Swagelok X Series PTFE-Attachment A and B

Reviewer's Notes:

As required by CSA B51 4.2.1, this registration expires on 16-Oct-2030. This CRN is valid until the expiry date as long as the Manufacturer maintains a valid quality control program verified by an acceptable third-party agency until that date. Should the certification of the quality control program lapse before the expiry date, this registration shall become void. Any additional conditions of registration stated in TSSA CRN# 0D22748.5 registration shall apply to BC registration.

(PROD) 30400-20 GST #: 87391 2802 RT0001



Toll Free: 1-866-566-7233 www.technicalsafetybc.ca

Contact me if you have any questions. The invoice for registration will be forwarded under separate cover.

Emilia Tam

emilia.tam@technicalsafetybc.ca Design Administration

cc:

(PROD) 30400-20 GST #: 87391 2802 RT0001



Technical Standards and Safety Authority 345 Carlingview Drive Toronto, Ontario M9W 6N9 www.tssa.org Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



(Name and Positi	ion, e.g. President, Plant Manage	r, Chief Engineer)	
of Swagelok Company	United to the state of the stat		
019	(Name of Manufacturer)		
ocated at 29500 Solon Road, Solon, Ohio 4413	9 USA	(440) 248-4600	(440) 349-5970
Located at 29500 Solon Road, Solon, Onio 4413 (Plant Address)	(2.816-03999V)	(Telephone No.)	(Fax No.)
do solemnly declare that the fittings listed here and Pressure Vessels Regulation, comply with	th all of the requirements	of	ds and Safety Act, Boiler
Association for Rubber Products Manufactur	Concession of the Concession o		*
which specifies the dimensions, materials of const	recognized North American Stand truction, pressure/temperature		ng the fittings and service;
as suppressure/temperature ratings and the basis for I further declare that the manufacture of these fittings which has been verified by the follow	is controlled by a quality sy	of the fitting for identification	and service.
The items covered by this declaration, for which I seek reg	100 March 1970	ose	type fittings. In support of
this application, the following information and/or test data a			typo mango, in oupport of
ISO 9001:2015 Certificate, Attachment A, Attachment		and other Support Docur	ments
(dra	wings, calculations, test reports,	etc.)	Ä
Declared before me at	in the		of
Journal Bolloto His de			
the day of	AD 20		
Commissioner for Oaths:			
		11,	7 11
Unable to get a notary sign			1//
seal due to COVID-19 situ	ation -	brel .	1011
seal due to COVID-19 situ	ation -	(Signature of	Declarer)
seal due to COVID-19 situ Septemberon 2020		(Signature of	
seal due to COVID-19 situ Septemberon 2020	FOR OFFICE USE ONL meets the requirements of t ssure Vessels Regulation, a	Y Standards he and Safety Authority	Boilers and Pressure Vessels Safety Program
Septembestorbure) 2020 For the best of my knowledge and belief, the application Technical Standards and Safety Act, Boilers and PrecSA Standard B51 and is accepted for registration in Cal	FOR OFFICE USE ONL meets the requirements of t essure Vessels Regulation, a ategory	Y Technical Standards and Safety Authority REGI	Boilers and Pressure Vessels
seal due to COVID-19 situ Septemberenbure) 2020 For the best of my knowledge and belief, the application Technical Standards and Safety Act, Boilers and Pre-	meets the requirements of tessure Vessels Regulation, a attegory This De has be	Y Technical Standards and Safety Authority REGIO	Boilers and Pressure Vessels Safety Program
September of COVID-19 situ September of Lure 2020 For the best of my knowledge and belief, the application Technical Standards and Safety Act, Boilers and Precision Standard B51 and is accepted for registration in Ca	rock of the requirements of the same vessels Regulation, a lategory	Technical Standards and Safety Authority REGI ocument en y signed amp size Signed: Signed	Boilers and Pressure Vessels Safety Program STERED



Canadian Registration Number Submittal
Category D Crimped Swagelok X Series PTFE Hose

THIS IS PART OF CRN
0D22748.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

September 1, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok X Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex XC and XT hose (X Series) and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

Х	Maximum Pressure (psig)					
Series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
1/4"	3500	3500	3075		Swagelok Tube Fitting [SL, SM] 1/8" – 2" (3-50mm)	
3/8"	3000	3000	1675	OR Smooth bore carbon black filled PTFE (XC Series)	Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2" Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1"	C Association for Rubber Products
1/2"	1800	1800	1665		Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2" Tube Butt Welds [TB] 1/2" – 1"	
3/4"	1250	1250	900	304 SS Braid Reinforcement End Connections 316 SS	Female VCO O-ring Face seal Fitting [VF] 1/8" – 2" Female VCR Metal Gasket Face seal Fitting [RF] 1/8" – 2" Male ISO/BSP Parallel Threads	Handbook
1"	1000	1000	895	Collar 300 series SS	W/ 60° Male cone (ISO 228) [MS] 1/4" – 1" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"	



Canadian Registration Number Submittal
Category D Crimped Swagelok X Series PTFE Hose


THIS IS PART OF CRN 0D22748.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety Program

September 1, 2020 Page 2 of 2

XT series is standard Swagelok virgin PTFE-lined hose with a fiber braid reinforcement and 304 stainless steel reinforcement with a silicone cover. The XC series consist of the same construction but has Swagelok carbon black filled virgin PTFE liner. The 1 inch nominal ID hose for both XT and XC series is constructed with two stainless steel braids and no fiber braid. All X Series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN
0D22748.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man