

Suite 600 - 2889 E 12th Ave Vancouver, BC V5M 4T5

Toll Free: 1-866-566-7233 www.technicalsafetybc.ca

TECHNICAL STANDARDS & SAFETY AUTHORITY 345 CARLINGVIEW DRIVE TORONTO ON M9W 6N9
 Date:
 November 18, 2020

 Account #:
 35231

 Journal #:
 76907

Attn: TSSA

Re: Application for Design Registration

The design, as detailed in your, 0D22750.5, for a Fitting is accepted for registration as follows:

Registered To: SWAGELOK COMPANY CRN: 0D22750.51

Drawing #: Scope of Registration

Drawing Revision: N/A

Conditions Of Registration:

This design was registered based on a technical review performed by the province of initial registration in accordance with the Association of Chief Inspectors policy on reciprocal recognition of design review.

Scope of Registration: Crimped Swagelok ST series PTFE - attachment A and B

Reviewer's Notes:

As required by CSA B51 4.2.1, this registration expires on 16-Oct-2030. This CRN is valid until the expiry date as long as the Manufacturer maintains a valid quality control program verified by an acceptable third-party agency until that date. Should the certification of the quality control program lapse before the expiry date, this registration shall become void. Any additional conditions of registration stated in TSSA CRN# 0D22750.5 registration shall apply to BC registration.



Suite 600 - 2889 E 12th Ave Vancouver, BC V5M 4T5

Toll Free: 1-866-566-7233 www.technicalsafetybc.ca

Contact me if you have any questions. The invoice for registration will be forwarded under separate cover.

Emilia Tam

emilia.tam@technicalsafetybc.ca Design Administration

cc:



Technical Standards and Safety Authority 345 Carlingview Drive Toronto, Ontario M9W 6N9 www.tssa.org Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below

Dmade

STATUTORY DECLARATION Registration of Fittings

	(Name and Position, e.g. I	President, Plant Manager, Ch	ief Engineer)		
of Swagelok Cor	mpany				
	(Nai	me of Manufacturer)			
Located at 29	500 Solon Road, Solon, Ohio 44139 USA		(440) 248-4600	(440) 349-5970	
	(Plant Address)		(Telephone No.)	(Fax No.)	
and Press	ly declare that the fittings listed hereunder, ure Vessels Regulation, comply with all of on for Rubber Products Manufacturers (Af	f the requirements of	e Technical Standard	Is and Safety Act, Boiler	
which speci	(Title of recogniz files the dimensions, materials of construction,	ed North American Standard) pressure/temperature rai		ng the fittings and service;	
3 	covered by the provisions of a recognized as supported b emperature ratings and the basis for such ra	ly the attached data whic	h identifies the dimensio	ons, material of construction	
I further declare th	hat the manufacture of these fittings is contr which has been verified by the following aut		n meeting the requirem	ents of ISO 9001:2015	
The items covered	by this declaration, for which I seek registration	02.10		type fittings. In support of	
this application, the	following information and/or test data are attac Certificate, Attachment A, Attachment B, (hed as follows:	d other Support Docun		
	(drawings, ca	alculations, test reports, etc.)			
				1	
Declared before	me at	in the		of	
the	day ofAD 20_				
Commissioner f					
Unable t seal due	o get a notary signatu Printed name: to COVID-19 situatio	re or on -	hell.	Talk	
Septemb	estimatives 2020	1	(Signature of I	Declarer)	
Technical Standa	FOR O knowledge and belief, the application meets t ards and Safety Act, Boilers and Pressure V 1 and is accepted for registration in Category	essels Regulation, and	Technical Standards and Safety Authority REGIST	Boilers and Pressure Vessels Safety Program	
CRN:	0D22750.5	-	C.R.N: 0D22750.5	LILL	
	11	TSSA This Document has been digitally signed The stamp size has	and the second strends of		
Registered by:	ww	been optmized for 11 x 17 documents	Date: October 16	6, 2020.	
Dated:	OCTOBER 16, 2020 For scope of registration see the stampe				
	istration expires on: OCTOBE		achment A and B	ion see the stamped	

*Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request. PV 09553 (04/17) Service applications: Liquid, Air or Gas service



Canadian Registration Number Submittal Category D Crimped Swagelok ST series PTFE Hose September 1, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok ST series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex ST series hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

ST Maximum Pressure (psig)							
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (400°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction	
1/8"	3000	3000	2550				
1/4"	3500	3500	3250	Summary Stress Summary Stress Main Stress 3250 Smooth Bore PTFE Main Stress Braid Synthetic Fiber Braid Main Stress 2350 Stress Main Stress 1800 End Connections Stress Main Stress 1800 End Connections Stress Main Stress 1250 Stress Stress Main Stress) Core Smooth Bore PTFE Male & Female NPT Fitting [PM, PF]	Swagelok Tube Fitting [SL SM] 1/8" – 2" (3 – 50mm) Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2"	pe
3/8"	3000	3000	2350		Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"	Association for Rubber Products Manufacturers	
1/2	1800	1800	1800		Cover Silicone cover Tube Butt Welds [TB] 00 End Connections Male & Female VCO O-rest	Tube Butt Welds [TB] 1/2" – 1" Male & Female VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	(ARPM) Hose "Handbook
3/4	1250	1250	1250		Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8"- 2" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"		
1"	1000	1000	1000				




Canadian Registration Number Submittal Category D Crimped Swagelok ST series PTFE Hose

Product Description

The Swagelok ST series hose is a virgin PTFE-lined hose with a fiber braid reinforcement and 304 stainless steel reinforcement with silicone cover. The exceptions are the 1/8-inch nominal size hose does not have the fiber braid and the 1 inch nominal size is constructed with two stainless steel braids and no fiber braid. All ST series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

0D22750.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety Program

THIS IS PART OF CRN

September 1, 2020 Page 2 of 2

Attachment A. Swagelok Manufacturing Locations Boilers and Pressure Vessels Safety Program

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Limited	
Changshu Export Process Zone	Ballafletcher Road	
Changshu Economic Development Zone	Tromode	
Changshu, Jiangshu	IM4 4RA	
215513 China	Isle of Man	