

9/23/2020

TSSA 345 Carlingview Drive Toronto, ON M9W 6N9 CA

Dear Cecylia Garbacz

#### Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 74-R975 CRN: 0D22658.54

Scope: NC SERIES HOSE ASSEMBLIES- ATTACHMENT A AND B

Manufacturer: SWAGELOK Expiry Date: 31/Aug/30

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at <a href="mailto:Cheryl.Lashek@gov.mb.ca">Cheryl.Lashek@gov.mb.ca</a> for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM

Inspection and Technical Services
Office of the Fire Commissioner
508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8
T (204) 945-3507 | F (204) 948-2309



Showfacsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



	STAT	UTORY DECL Registration of Fitt		
I loel Feldman	Vice President of Engineering	B		
I, Joer returnan,		n, e.g. President, Plant Manager,	Chief Engineer)	
C	0.580.000 (0.000 to 0.000 to 0	.,	31171 - 11311-77	
of Swagelok Cor	mpany	(Name of Manufacturer)		
Ha		an equality and		
Located at 29	500 Solon Road, Solon, Ohio 4413! (Flant Address)	USA	(440) 248-4600	(440) 349-5970
	(Plant Address)		(Telephone No.)	(Fax No.)
and Press	ly declare that the fittings listed here ure Vessels Regulation, comply wit roducts Manufacturers (ARPM) Hos	h all of the requirements o		ls and Safety Act, Boilers
which speci	(Title of r ifies the dimensions, materials of constr	ecognized North American Standa uction, pressure/temperature		ig the fittings and service;
or are not	covered by the provisions of a recog	nized North American stan		
pressure/te	emperature ratings and the basis for s			
I further declare th	hat the manufacture of these fittings is which has been verified by the follow		tem meeting the requirement	ents of ISO 9001:2015
The items covered	by this declaration, for which I seek regi		se	type fittings. In support of
this application, the	following information and/or test data ar Certificate, Attachment A, Attachme	e attached as follows:		LA PARTIES
-	(drav	vings, calculations, test reports, et	tc.)	-
Declared before	me at	in the		of
the	day of	AD 20		
Commissioner f	or Oaths:			
Unable to	get a notary signa	ture		
Chable to	(Printed name)	ture		
or seal du	(Printed name) ie to Covid-19 situ:	ation	Lel ( Fe	//_
August 1	0(s@ <b>6</b> @e0)		(Signature of L	Declarer)
rugust 1			A Table 1	J-73-33-32, \$41)
Technical Standa	Fi knowledge and belief, the application r ards and Safety Act, Boilers and Pres 1 and is accepted for registration in Ca	sure Vessels Regulation, an	e Technical Standards	Boilers and Pressure Vessels Safety Program
CRN:	0D22658.5	This Doc	REGIS'	TERED
Registered by:	M	TSSA signed The star has beer optimize	np size nd for 11 x  C.R.N.: 0D22658.8	5 %
Dated.	AUG 31, 2020	17 docu	Date: August 3	
NOTE: This roa	istration expires on: ALIG 3		the scope of registration	

<sup>\*</sup>Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.



Canadian Registration Number Submittal
Category D Crimped Swagelok NC series PTFE Hose

THIS IS PART OF CRN
0D22658.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

June 22, 2020 Page 1 of 2

## Attachment B: Scope of Registration for Crimped Swagelok NC series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (NC series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

#### **Summary Table**

NC	Maximum Pressure (psig)					
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
3/8"	1250	1250	140	<u>Core</u> Convoluted Bore Carbon Black- filled (PTFE)	Swagelok Tube Fitting [SL SM]  1/8" – 2" (3-50mm)  Male & Female NPT Tapered Pipe Fitting [PM PF]  1/8" – 2"  Male and Female ISO/BSP Tapered (ISO 7) Pipe Threads  [MT FT]	
1/2"	720	750	130	Covered By Ceramic Insulating Wrap  Braid Aramid Fiber Braid Reinforcement	1/4" – 1"  Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"  Tube Butt Welds [TB] 1/2" – 1"  Female & Male VCO O-ring Face seal Fitting [VF, VM]	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
3/4"	375	375	80	Connections 316 SS  Crimp on Collar 300 series SS	1/8" - 2"  Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8" - 2"  Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4"- 1"	

#### **Product Description**

NC series is standard Swagelok virgin Convoluted PTFE-lined hose with a Nomex insulating wrap and fiber braid reinforcement. All NC series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).



Canadian Registration Number Submittal Category D Crimped Swagelok NC series PTFE Hose

## THIS IS PART OF CRN 0D22658.5

Technical Standards and Safety Authority


Boilers and Pressure Vessels Safety

Program

June 22, 2020 Page 2 of 2

#### **Configurations**

All end connection inserts are crimped onto the hose using crimp collars.



#### **Product Options**:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

#### **Cover Options**

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

#### **Tag and Marking Options**

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

#### **End Connection Seals or Sealants Options**

- VCO O-rings
- Pipe Thread ends thread sealant

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

# THIS IS PART OF CRN 0D22658.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety

### **Attachment A. Swagelok Manufacturing Locations**

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	