

4/6/2020

TSSA 345 Carlingview Drive Toronto, ON M9W 6N9

Dear Cecylia Garbacz

## Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 74-R552 CRN: 0C22209.54

Scope: Scope of Registration: SWAGELOK D Series Needle Valves (Cat C)

Manufacturer: SWAGELOK Expiry Date: February 27, 2030

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at Cheryl.Lashek@gov.mb.ca for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM

Inspection and Technical Services
Office of the Fire Commissioner
508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8
T (204) 945-3507 | F (204) 948-2309



Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



STATUTORY DEC		
Registration of	Fittings	
, Joel Feldman, Vice President of Engineering		
(Name and Position, e.g. President, Plant Manu	iger, Chief Engineer)	
of Swagelok Company		
(Name of Manufacturer)		
Located at 29500 Solon Road, Solon, Ohio 44139 USA	(440) 248-4600	(440) 349-5970
(Plant Address)	(Telephone No.)	(Fax No.)
do solemnly declare that the fittings listed hereunder, which are subjet and Pressure Vessels Regulation, comply with all of the requirement ASME B31.1 for unlisted components, and ASME B31.3 for unlisted	ts of	Is and Safety Act, Boilers
(Title of recognized North American St	landard)	
which specifies the dimensions, materials of construction, pressure/tempera	ture ratings, identification markin	ig the fittings and service;
or are not covered by the provisions of a recognized North American sas supported by the attached da		
pressure/temperature ratings and the basis for such ratings, the marking		
I further declare that the manufacture of these fittings is controlled by a quality which has been verified by the following authority, BSI	system meeting the requirement	ents of ISO 9001:2015
The items covered by this declaration, for which I seek registration, are category C.	Valves	type fittings. In support of
this application, the following information and/or test data are attached as follows: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information		
(drawings, calculations, test report		icina
Declared before me at Salonin the	state	of Ohio
the 25t day of 100 AD 20 19.		
Commissioner for Oaths:		
Brenda Hammel		
(Printed name)	11.2	//
Berda James	feel (17d	
(Signature)	(Signature of C	Declarer)
FOR OFFICE USE ON		Boilers and
To the best of my knowledge and belief, the application meets the requirements of	of theand Safety	Pressure Vessels
Technical Standards and Safety Act, Boilers and Pressure Vessels Regulation	and Authority OFF	Safety Program
CSA Standard B51 and is accepted for registration in Category	REGIST	ERED
CRN: 0C22209,5		- WWW. 102-
Registered by	C.R.N OC.222	209,5
Dated: Feb. 27, 2020	Signed:	2 2-20
NOTE: This registration expires on: Feb 27 2030	Date: 166.27	1.4020

\*Information provided in this application is releasable under the Freedom of Information and Privacy
Protection Act and may be disclosed upon request.

PV 09553 (04/17)

For Scope of tregistration fee attacked stamped

Attach went A and B

February 17, 2020 Page 1 of 3

# Attachment B: Scope of CRN Registration for Swagelok D Series Needle Valves (Category C)

This document represents the scope of the Swagelok D Series Needle Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

#### Summary Table

Series Bearing	Main Pressure	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure (psig)		Design Code
	Bearing Component			At -65 to 100°F	@ max temperature	of Construction
OD	Body	F316 SS (ASTM A182)	Tube Fitting 1/8" Female NPT 1/8" Male NPT 1/8"	3000	2065 @ 450°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
14D	Body	F316 SS (ASTM A182)	Tube Fitting 1/4", 6MM Male NPT 1/4"	3000	2065 @ 450°F	
16D	Body	F316 SS (ASTM A182)	Tube Fitting 3/8" Female NPT 1/4" Male NPT 1/4", 3/8",1/2"	3000	2065 @ 450°F	
14D	Body	Alloy 400 (ASTM B564)	Tube Fitting 1/4", 6MM Male NPT 1/4"	3000	2380 @ 450°F	
16D	Body	Alloy 400 (ASTM B564)	Tube Fitting 3/8" Female NPT 1/4" Male NPT 1/4", 3/8",1/2"	3000	2380 @ 450°F	
OD	Body	Brass C37700 (ASTM B283)	Tube Fitting 1/8" Female NPT 1/8" Male NPT 1/8"	3000	2350 @ 200°F	ASME B31.1 (Unlisted Components)
14D	Body	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 6MM Male NPT 1/4"	3000	2350 @ 200°F	
16D Body	Body	Brass C37700	Female NPT 1/4" Male NPT 1/4",3/8",1/2"	3000	2350 @ 200°F	
	body	(ASTM B283)	Tube Fitting 3/8"	2200	1760 @ 200°F	



Canadian Registration Number Submittal #D-NEEDLE-2019
Category C: Swagelok Needle Valves

February 17, 2020 Page 2 of 3

Series Bearing		Material	Port Connections,	Maximum Rated Pressure (psig)		Design Code
	Bearing Component		Sizes	At -65 to 100°F	@ max temperature	Construction
OD	Body	Brass C37700 (ASTM B283)	Tube Fitting 1/8" Female NPT 1/8" Male NPT 1/8"	3000	390 @ 400°F	ASME B31.3 (Unlisted Components)
14D	Body	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 6MM Male NPT 1/4"	3000	390 @ 400°F	
16D Body	Brass C37700	Female NPT 1/4" Male NPT 1/4",3/8",1/2"	3000	390 @ 400°F		
	(ASTM B283)	Tube Fitting 3/8"	2200	2200 390 @ 400°F		

### **Product Illustrations**



#### **Typical Product Characteristics:**

Some of the product options listed below could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:


#### Valve Seat Material

PCTFE PEEK

#### Stem Seal Material

Fluoroelastomer (FKM) – standard Perfluoroelastomer (FFKM) Nitrile Ethylene propylene Silicone





Canadian Registration Number Submittal #D-NEEDLE-2019
Category C: Swagelok Needle Valves

February 17, 2020 Page 3 of 3

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

D Series Needle Valve Catalog MS-01-42, Rev H



# Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohic 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Limited
Changshu Export Process Zone	Ballafletcher Road
Changshu Economic Development Zone	Tromode
Changshu, Jiangshu	IM4 4RA
215513 China	Isle of Man

