

8/12/2020

TSSA 345 Carlingview Drive Toronto, ON M9W 6N9

Dear Cecylia Garbacz

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number:74-R848CRN:0C22514.54Scope:Scope of RegistrationManufacturer:SWAGELOKExpiry Date:22/Jun/30

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at <u>Cheryl.Lashek@gov.mb.ca</u> for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM Inspection and Technical Services Office of the Fire Commissioner 508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8 T (204) 945-3507 | F (204) 948-2309



Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



	S	FATUTORY Registrat	DECLA		
I loel Feldman	, Vice President of Enginee		1919-199-1919 1919-199-1919	81	
I,		and Position, e.g. President	Plant Manager, Ch	ef Engineer)	Ri
of Swagelok Co		-		and the second	
01 <u></u>	inipany.	(Name of Ma	nufacturer)		
	1500 Solon Road, Solon, Oh	io 1/139 ISA		(440) 248-4600	(440) 349-5970
Located at 20	9500 Solon Road, Solon, Oh (Plant Add			(Telephone No.)	(Fax No.)
and Press	nly declare that the fittings lis sure Vessels Regulation, co	mply with all of the re-	quirements of		Is and Safety Act, Boilers
ASME D.	31.1 for unlisted component	(Title of recognized North			17
which spec	cifies the dimensions, materials				ng the fittings and service;
pressure/te	covered by the provisions of emperature ratings and the b that the manufacture of these	as supported by the at asis for such ratings, the fittings is controlled by	tached data whic he marking of the / a quality system	h identifies the dimension e fitting for identification	ons, material of construction, and service.
	which has been verified by				
	d by this declaration, for which I			1	_ type fittings. In support of
	e following information and/or te Certificate, Attachment A, A			d other Support Desur	nonta
130 3001 2015	Cerimicate, Attaciment A, A	(drawings, calculation	and the second s	office Support Docum	lienis
		forennige, serenener	of icon reported crost		
Declared before	e me at		in the	ñ	of
the	day of	AD 20	_*		
Commissioner 1	for Oaths:				
Unable to s	get a notary signati	ire or seal			
	idense Ju			16.7	11_
	(Signature)			(Signature of I	Declarer)
Technical Standa	knowledge and belief, the app ards and Safety Act, Boilers i1 and is accepted for registrat	and Pressure Vessels	irements of the	Technical Standards and Safety Authority REGIST	Boilers and Pressure Vessels Safety Program
CRN:	0C22514.5	G	This Document been digitally		
Registered by:	_el		signed The stamp size been optimized 11 x 17 docume	for	2020.
Dated:	JUNE 22, 2020			FOR SCOPE OF RE	EGISTRATION SEE
NOTE: This red	gistration expires on: J	UNE 22, 2030	-	STAMPED ATTACH	IMENT A AND B

*Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request. PV 09553 (04/17)



Canadian Registration Number Submittal Category C: Swagelok Metering Valves

Attachment B: Scope for Swagelok 31, S, M, and L Series Metering Valves (Category C)

This document represents the scope of the Swagelok 31, S, M, and L Series Metering Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

Product	Main	Main Pressure Bearing Material (Standard)		Maximum Ra (ps	Design Code		
Series	Pressure Bearing Component		Port Connections, Sizes	At -10 to 100°F (except 31 Series)	At max temperature	of Construction	
31	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/4",6MM Female NPT 1/8",1/4"	5000 @ -65 to 100°F	3435 @ 450°F 2815 @ 850°F		
S	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/16", 1/8",1/4", 3MM,6MM Male VCR 1/4"	2000	2000 @ 400°F	ASME B31.1 (Unlisted	
М	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8" Male VCR 1/4"	1000	1000 @ 400°F	Components) and ASME B31.3 (Unlisted Components)	
L	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 400°F		
S	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/16", 1/8",1/4", 3MM,6MM	2000	2000 @ 200°F		
М	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8"	1000	1000 @ 200°F	ASME B31.1 (Unlisted Components)	
L	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 200°F		
S Body, Bonnet		Brass C37700 (ASTM B283)	Tube Fitting 1/16", 1/8", 1/4", 6MM	2000	2000 @ 300°F		
	Donnet		Tube Fitting 3MM	2000	1885 @ 300°F		
М	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8"	1000	1000 @ 300°F	ASME B31.3 (Unlisted Components)	
L	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 300°F		



Canadian Registration Number Submittal Category C: Swagelok Metering Valves

Product Illustration

Date: June 5, 2020 Page 2 of 2



Typical Product Characteristics

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. Examples of these would include stem seal materials and handles.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

• 31, S, M, L Series Metering Valves Catalog MS-01-142, R11

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA THIS IS PART OF CRN 0C22514.5 Technical Standards and Safety Authority
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Limited
Changshu Export Process Zone	Ballafletcher Road
Changshu Economic Development Zone	Tromode
Changshu, Jiangshu	IM4 4RA
215513 China	Isle of Man