

5/7/2020

TSSA 345 Carlingview Drive Toronto, ON M9W 6N9

Dear Cecylia Garbacz

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 74-R600 CRN: 0C22234.54

Scope: CATALOG MS-01-164

Manufacturer: SWAGELOK Expiry Date: 10/Mar/30

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at Cheryl.Lashek@gov.mb.ca for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM

Inspection and Technical Services
Office of the Fire Commissioner
508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8
T (204) 945-3507 | F (204) 948-2309



Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



Swagelok Company (Name of Manufacturer) cated at 29500 Solon Road, Solon, Ohio 44139 USA (Plant Address) do solemnly declare that the fittings listed hereunder, which are subject to	(440) 248-4600	
(Name of Manufacturer) cated at 29500 Solon Road, Solon, Ohio 44139 USA (Plant Address) do solemnly declare that the fittings listed hereunder, which are subject the subject that the fittings listed hereunder.	(440) 248-4600	THE REPORT OF THE PARTY OF THE
(Plant Address) do solemnly declare that the fittings listed hereunder, which are subject t	(440) 248-4600	
(Plant Address) do solemnly declare that the fittings listed hereunder, which are subject t		(440) 349-5970
	(Telephone No.)	(Fax No.)
and Pressure Vessels Regulation, comply with all of the requirements of ASME B31.1 for unlisted components, and ASME B31.3 for unlisted components.	of	ls and Safety Act, Boilers
(Title of recognized North American Stand which specifies the dimensions, materials of construction, pressure/temperature		g the fittings and service;
or are not covered by the provisions of a recognized North American star		
pressure/temperature ratings and the basis for such ratings, the marking of		
office declars that the man feet up of these fittings is anothered by a configura-		
urther declare that the manufacture of these fittings is controlled by a quality sy which has been verified by the following authority, BSI	stem meeting the requireme	ints of 100 300 120 13
e items covered by this declaration, for which I seek registration, are category C. Va	lives	type fittings. In support of
s application, the following information and/or test data are attached as follows:		7416 :3.4 AV
O 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information		nents
(drawings, calculations, test reports, e	etc.)	
day of NO AD 20 19. mmissioner for Oaths: Sendo Hommel (Printed name) (Signature)	echnical (Signature of I	Declarer)
	forwignets AV	The second secon
the best of my knowledge and belief, the application meets the requirements of chnical Standards and Safety Act, Boilers and Pressure Vessels Regulation A Standard B51 and is accepted for registration in Category	adnosay - Sa	fety Program
N: 000000000000000000000000000000000000	RN: OC 222	34,5
gistered by:	Igned: Alacal	10.200
ted: March 10, 2020 Date	ate: TYTAT CM	10,2020
OTE: This registration expires on: March 10, 2030		114427
F.I.		Charles a response particular
ormation provided in this application is releasable under the	Freedom of Informa	ntion and Privacy
ormation provided in this application is releasable under the tection Act and may be disclosed upon request. For cape of registration of the state		CO



Canadian Registration Number Submittal
Category C: Swagelok Integral Bonnet Needle Valves

Attachment B: Scope of Registration for Swagelok O, 1, 18, 20 and 26 Series Integral Bonnet Needle Valves (Category C)

This document represents the scope of the Swagelok O, 1, 18, 20 and 26 Series Needle Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

THIS IS PART OF CRN

Summary Table

0C22234.5
Technical Standards and Safety Authority

Date: February 7, 2020

Page 1 of 3

					Boilers and Pressure V num Rateo ogram ure (psig)	essels Safety
Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	At -65 to 100°F (except Carbon Steel)	@ max. temperature	Design Code of Construction
O, 1, 18 Body	F316 SS (ASTM A182)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 3/4", 3MM, 6MM, 8MM, 10MM, 12MM, 18MM Female NPT 1/8", 1/4" Male NPT 1/8", 1/4", 3/8" Female ISO 1/4"	5000	3130 @ 600°F		
			Female NPT 3/8", 1/2" Female ISO 3/8", 1/2" Male NPT 1/2"	4400	2770 @ 600°F	
		F316 SS (ASTM A479)	Tube Fitting 1/4", 3/8", 1/2" Female NPT 1/4" Male NPT 1/4" 3/8", 1/2", 3/4" Female ISO 1/4"	6000	3760 @ 600°F	ASME B31.1 (Unlisted Components)
20, 26	Body		Female NPT 3/8"	5300	3330 @ 600°F	and ASME B31.3 (Unlisted
			Female NPT 1/2" Female ISO 1/2"	4900	3080 @ 600°F	Components)
1, 18	Body	Type 1137 Carbon Steel (ASTM 181)	Tube Fitting 1/4", 3/8", 1/2", 3/4", 6MM, 8MM, 10MM, 12MM, 18MM Female NPT 1/4", 3/8", 1/2" Male NPT 1/4", 3/8", 1/2" Female ISO 1/4", 3/8", 1/2"	3000 @ -20°F to 100°F	2615 @ 350°F	
O, 1	Body	Alloy 400 (ASTM B564)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 3/4", 8MM, 10MM Female NPT 1/8", 1/4" Male NPT 1/8", 1/4", Female ISO 1/4"	3000	2375 @ 500°F	



Swagelok
Canadian Registration Number Submittal
Category C: Swagelok Integral Bonnet Needle Valves

Product	Main Pressure	Main Pressure Bearing	Port Connections and Sizes	Maximum Rated Pressure (psig)		Design Code of
Series	Bearing Component	Material (Standard)		At -65 to 100°F	@ max. temperature	Construction
			Tube Fitting 1/8",1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4", 1/2"	3000	2350 @ 200°F	
THIS 0C2223	IS PART OF (RN	Tube Fitting 3/8"	2200	1760 @ 200°F	
I I	Standards and Safety and Pressure Vessels Program	· •	Tube Fitting 1/2"	2100	1680 @ 200°F	
			Tube Fitting 3/4"	1800	1440 @ 200°F	
			Tube Fitting 8MM	2320	1858 @ 200°F	ASME B31.1 (Unlisted
			Tube Fitting 10MM	1885	1509 @ 200°F	Components)
			Tube Fitting 12MM	2030	1625 @ 200°F	
			Tube Fitting 18MM	1590	1277 @ 200°F	
		Brass	Female NPT 3/8" Female ISO 3/8"	2600	2340 @ 200°F	
O, 1, 18	Body	C37700 (ASTM B283)	Female NPT 1/2" Female ISO 1/2"	2400	2160 @ 200°F	
			Tube Fitting 1/8",1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4", 1/2"	3000		
			Tube Fitting 3/8"	2200		
			Tube Fitting 1/2"	2100		
			Tube Fitting 3/4"	1800	390 @	ASME B31.3
			Tube Fitting 8MM	2300	400°F	(Unlisted Components)
			Tube Fitting 10MM	1885		
			Tube Fitting 12MM	2030		
			Tube Fitting 18MM	1590		
			Female NPT 3/8", 1/2" Female ISO 3/8", 1/2"	2400		

Date: February 7, 2020 Page 2 of 3



Canadian Registration Number Submittal
Category C: Swagelok Integral Bonnet Needle Valves

Product Illustrations



THIS IS PART OF CRN

Date: February 7, 2020

Page 3 of 3

0C22234.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Configurations

Bodies are available in straight pattern and angle pattern.

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Packing Options

Polytetrafluoroethylene (PFA) Ultra High Molecular Weight Polyethylene (UHMWPE) Polyetheretherkeytone (PEEK)

O-ring Stem Seal Options

Nitrile Ethylene Propylene Silicone Kalrez

Stem Designs

Regulating
PCTFE soft-seat regulating
PTFE soft-seat regulating

Additional options and non-pressure boundary alterations that do not affect pressuretemperature ratings may be made available within the scope of this registration. Examples of these would include handle options, actuator options, etc.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

O, 1, 18, 20 and 26 Series Needle Valve Catalog MS-01-164, Rev N

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Limited
Changshu Export Process Zone	Ballafletcher Road
Changshu Economic Development Zone	Tromode
Changshu, Jiangshu	IM4 4RA
215513 China	Isle of Man

