

10/26/2020

TSSA 345 Carlingview Drive Toronto, Ontario M9W 6N9 CA

Dear Cecylia Garbacz

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number:74-R1023CRN:0C22706.54Scope:Sno-Trik 410, 445, 645 and 945 Series- See the stamped attachment A and BManufacturer:SONDEX INC.Expiry Date:28/Sep/30

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at <u>Cheryl.Lashek@gov.mb.ca</u> for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM Inspection and Technical Services Office of the Fire Commissioner 508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8 T (204) 945-3507 | F (204) 948-2309



Technical Standards and Safety Authority 345 Carlingview Drive Toronto, Ontario M9W 6N9 www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below

Swagelo 6

STATUTORY DECLA Registration of Fittin	and the second se							
I. Joel Feldman, Vice President of Engineering	8							
(Name and Position, e.g. President, Plant Manager, Chi	ef Engineer)	S.						
of Swagelok Company	201958000							
(Name of Manufacturer)		53						
Located at 29500 Solon Road, Solon, Ohio 44139 USA	(440) 248-4600 (Telephone No.)	(440) 349-5970 (Fax No.)						
	discould be a second of the second of the second	1/#-02041.AVX#5						
do solemnly declare that the fittings listed hereunder, which are subject to the and Pressure Vessels Regulation, comply with all of the requirements of ASME B31.1 for unlisted components, and ASME B31.3 for unlisted comp		ls and Safety Act, Boilers						
(Title of recognized North American Standard)								
which specifies the dimensions, materials of construction, pressure/temperature rati	ings, identification markin	g the fittings and service;						
or are not covered by the provisions of a recognized North American standar as supported by the attached data which pressure/temperature ratings and the basis for such ratings, the marking of the	h identifies the dimensio	ns, material of construction,						
I further declare that the manufacture of these fittings is controlled by a quality system which has been verified by the following authority, <u>BSI</u>		24						
The items covered by this declaration, for which I seek registration, are category C. Valve		type fittings. In support of						
this application, the following information and/or test data are attached as follows:	Lather Support Dooup							
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and (drawings, calculations, test reports, etc.)	other Support Docum	nents						
ferannika, oaronanona, see sebena, see								
Declared before me at in the		of						
the day of AD 20								
Convisioner for gette a notary signature								
or seal dug to Covid and Ovid	111-	11						
situation - August 27, 2020	hell. 7	il _						
(Signature)	(Signature of L	Declarer)						
FOR OFFICE USE ONLY To the best of my knowledge and belief, the application meets the requirements of the Technical Standards and Safety Act, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category <u>C</u> .	Technical Standards and Safety Authority REGIS	Boilers and Pressure Vessels Safety Program						
CRN- 0C22706.5 This Docume	ent	and the second second						
CRN:		5.5						
Registered by:	11 Deter Senten	nber 28, 2020.						
Dated: SEPT 28, 2020	Control of the	: See the stamped						
	ttachment A and B.							

*Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request. PV 09553 (04/17)

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Limited
Changshu Export Process Zone	Ballafletcher Road
Changshu Economic Development Zone	Tromode
Changshu, Jiangshu	IM4 4RA
215513 China	Isle of Man



Canadian Registration Number Submittal Category C: Swagelok Sno-Trik High Pressure Needle Valves

Attachment B. Scope of CRN Registration for Swagelok Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves (Category C)

This document represents the scope of the Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves covered by this submission for CRN approval. The 410 Series Valves were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components, while the 445, 645 and 945 High-Pressure Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX for unlisted components.

Summary Table

	Main	Main Pressure	Pressure Press		um Rated ire (psig)	Design Code
Product Series	Pressure Bearing Component	Bearing Material (Standard)	Port Connections and Sizes	At –65 to 100°F	At maximum temperature	of Construction
410	Body	316 SS (ASTM A479)	Female NPT 1/4"	15,000	6085 @ 850°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
445 Body	316 SS	Swagelok straight thread high-pressure Female 9/16"	45,000	33,400 @ 450°F		
	-	(ASTM A479)	Medium Pressure 1/4"	20,000	18,600 @ 450°F	
645 Body	316 SS	Swagelok straight thread high-pressure Female 3/4	45,000	33,400 @ 450°F	ASME B31.3 Chapter IX	
	, (ASI	(ASTM A479)	Medium Pressure 3/8"	20,000	18,600 @ 450°F	(Unlisted Components)
945	Rody	316 SS	Swagelok straight thread high-pressure Female 1-1/8	45,000	33,400 @ 450°F	
		(ASTM A479)	Medium Pressure 1/2"	20,000	18,600 @ 450°F	

THIS IS PART OF CRN 0C22706.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety Program



Canadian Registration Number Submittal Category C: Swagelok Sno-Trik High Pressure Needle Valves Date: August 13, 2020 Page 2 of 2

Product Illustration



THIS IS PART OF CRN 0C22706.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety Program

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are equal to or less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Material

440C SS S17400 SS

Stem Seal Material

Glass-Filled PTFE Grafoil

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

 Medium and High-Pressure Fittings, Tubing, Valves and Accessories Catalog MS-02-472, Rev M