UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company	
MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 441	39 USA
PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio	
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CA	TEGORY ONLY TITLE OF THE STANDARD OF CONSTRUCTION
A Pipe fittings, including couplings, tees, elbows, Ye, plugs, unions, pipe caps, B Flanges: all flanges C Valves: all line valves	or reducers ASME B31.1 for unlisted components,
D Expansion joints, flexible connections, and hose assemblies: all types	ASME B31.3 for
E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, k	evels, or unlisted components
pressure transmitters	CANCO MANORANA ANTARANA MANORANA DA SA
G Certified capacity-rated pressure relief devices acceptable as primary over pribollers, pressure vessels, piping and fusible plugs	essure protection on
H Pressure retaining components that do not fall into one of the above categories	77 TSLOVE VI
N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APP	
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APP	FORGED () WELDED () WROUGHT ()
C -1.1	CAST O OTHER O
SMUUDION	
Chagoioic	
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE	ACTUAL ITEMS TO BE REGISTERED:
ISO 9001:2015 Certificate, Attachment A, Attachment B, Calalog Infor	madon and odice support socialisms
ny knowledge represents the product for which registration is sought. It emperature ratings, and identification markings are in accordance with manufacture of these fittings is regulated by a Quality Control Program for in part and has been verified by <u>ESI</u> declaration conscientiously believing it to be true, and knowing that it is	the herein named standards. I further declare that the which extends to each plant where fabrication occurs in whole as being suitable for that purpose and I make this solemn
Signature of Declarer: Auc C. Published	
Declared before me at Unable to get a notary sign	mature THIS SPACE FOR THE
Thisday of or seal due to COVID-19	OFFICIAL SEAL
Commissioner of Cathe or Notary Public (sign) <u>Situation - August 27, 20</u> (Affix Official seal to the right)	20
This space for Regulato	ry Authority use
This registration must be revalidated after ten	75. (0): FSD
CRN: 0C22706.5	NUNAVUT
FID#:1214	Boilers and
Sno-Trik 410 (B31.1, B31.3), 445, 645 and 945 (B31.3 Chapt.IX) series HP needle valves.	Nunavut Pressure Vesseis Act
All fittings shall be registered in the name of the Manufacturer.	REGISTERED
I forms and one copy of supporting documentation.	CRN 00227706.5 N
3. The declaration shall be made by the person having full authority and	Date Oct 30 2000
responsibility for the quality of the end product.	00,000
at a maximum interval of five (5) years.	Signed Miles !
CRN expires Sept.28th, 2030 - DG	Chief to spector
	Territorial Registration Fee



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Attachment B. Scope of CRN Registration for Swagelok Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves (Category C)

This document represents the scope of the Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves covered by this submission for CRN approval. The 410 Series Valves were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components, while the 445, 645 and 945 High-Pressure Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX for unlisted components.

Summary Table

	Main	Main Pressure			um Rated ire (psig)	Design Code
Product Series	Pressure Bearing Component	Bearing Material (Standard)	Port Connections and Sizes	At -65 to 100°F	At maximum temperature	of Construction
410	Body	316 SS (ASTM A479)	Female NPT 1/4"	15,000	6085 @ 850°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
445 Body	316 SS	Swagelok straight thread high-pressure Female 9/16"	45,000	33,400 @ 450°F		
	·	(ASTM A479)	Medium Pressure 1/4"	20,000	18,600 @ 450°F	
645 Body	316 SS	Swagelok straight thread high-pressure Female 3/4	45,000	33,400 @ 450°F	ASME B31.3 Chapter IX	
		(ASTM A479)	Medium Pressure 3/8"	20,000	18,600 @ 450°F	(Unlisted Components)
945	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 1-1/8	45,000	33,400 @ 450°F	
			Medium Pressure 1/2"	20,000	18,600 @ 450°F	

THIS IS PART OF CRN

Date: August 13, 2020

Page 1 of 2

0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Product Illustration



THIS IS PART OF CRN 0C22706.5

Date: August 13, 2020

Page 2 of 2

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are equal to or less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Material

440C SS S17400 SS

Stem Seal Material

Glass-Filled PTFE Grafoil

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

 Medium and High-Pressure Fittings, Tubing, Valves and Accessories Catalog MS-02-472, Rev M

THIS IS PART OF CRN 0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man