

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



STA	ATUTORY DECLA Registration of Fitti		·
Joel Feldman, Vice President of Engineering		•	
7	9 I Position, e.g. President, Plant Manager, Cl	nief Engineerl	
0.590.000.000			
of Swagelok Company			
	(Name of Manufacturer)		
Located at 29500 Solon Road, Solon, Ohio (Plant Address	44139 USA	(440) 248-4600	(440) 349-5970
(Plant Addres	es)	(Telephone No.)	(Fax No.)
do solemnly declare that the fittings listed and Pressure Vessels Regulation, comp	ly with all of the requirements of	ne Technical Standard	Is and Safety Act, Boilers
Rubber Products Manufacturers (ARPA	II) HOSB Handbook Title of recognized North American Standard	1	- T
which specifies the dimensions, materials of			ng the fittings and service;
or are not covered by the provisions of a	recognized North American standa supported by the attached data whi		
pressure/temperature ratings and the bas			
I further declare that the manufacture of these fitt which has been verified by the		m meeting the requirem	ents of ISO 9001:2015
The items covered by this declaration, for which I see			type fittings. In support of
this application, the following information and/or test of	31 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		_ type mangs. In support of
ISO 9001:2015 Certificate, Attachment A, Atta		d other Support Docun	nents
=	(drawings, calculations, test reports, etc.)		<del></del>
Declared before me at	in the		of
the day of	AD 20		
Commissioner for Oaths:			
Unable to get a notary sig	gnature		
or seal due to Covid-19 s	ituation	6/17	//_
August 10,92020		(Signature of L	Declarer)
\$1 E	FOR OFFICE USE ONLY	-	
To the best of my knowledge and belief, the applic Technical Standards and Safety Act, Boilers and CSA Standard B51 and is accepted for registration	ation meets the requirements of the d Pressure Vessels Regulation, and	Technical Standards and Safety Authority	Boilers and Pressure Vessels Safety Program
	ili Galegoly		
CRN: 0D22658.5	This Docum	ent gitally	TERED
Registered by:	TSSA signed The stamp in as been optimized to	ritx Signed:	5
AUG 31, 2020	17 docume	Date: August 3	STATE OF TAXABLE
NOTE: This registration expires on: AL		e scope of registration ed documents ( atta	on see the attached chment A and B)

<sup>\*</sup>Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.



Canadian Registration Number Submittal
Category D Crimped Swagelok NC series PTFE Hose

THIS IS PART OF CRN
0D22658.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

June 22, 2020 Page 1 of 2

## Attachment B: Scope of Registration for Crimped Swagelok NC series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (NC series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

#### **Summary Table**

NC	Maximum Pressure (psig)					
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
3/8"	1250	1250	140	Core Convoluted Bore Carbon Black- filled (PTFE)	Swagelok Tube Fitting [SL SM]  1/8" – 2" (3-50mm)  Male & Female NPT Tapered Pipe Fitting [PM PF]  1/8" – 2"  Male and Female ISO/BSP Tapered (ISO 7) Pipe Threads  [MT FT]	
1/2"	720	750	130	Covered By Ceramic Insulating Wrap  Braid Aramid Fiber Braid Reinforcement	1/4" – 1"  Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS]  1/4" – 2"  Tube Butt Welds [TB]  1/2" – 1"  Female & Male VCO O-ring Face seal Fitting [VF, VM]	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
3/4"	375	375	80	Connections 316 SS  Crimp on Collar 300 series SS	1/8" - 2"  Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8" - 2"  Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4"- 1"	

#### **Product Description**

NC series is standard Swagelok virgin Convoluted PTFE-lined hose with a Nomex insulating wrap and fiber braid reinforcement. All NC series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).



Canadian Registration Number Submittal
Category D Crimped Swagelok NC series PTFE Hose

THIS IS PART OF CRN 0D22658.5

Technical Standards and Safety Authority


Boilers and Pressure Vessels Safety

Program

June 22, 2020 Page 2 of 2

#### **Configurations**

All end connection inserts are crimped onto the hose using crimp collars.



#### **Product Options**:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

#### **Cover Options**

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

#### **Tag and Marking Options**

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

#### **End Connection Seals or Sealants Options**

- VCO O-rings
- Pipe Thread ends thread sealant

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

# THIS IS PART OF CRN 0D22658.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety

### **Attachment A. Swagelok Manufacturing Locations**

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man