UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

MANUFACTURERS NAME: MANUFACTURERS ADDRES PLANT LOCATIONS: Head	YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
PLANT LOCATIONS: Head	Swagelok Company		
PLANT LOCATIONS: Head	SS: 29500 Solon Road	l, Solon, Ohio 44139 USA	
CATEGORY OF THE	Iquarters: 29500 Solon	Road, Solon, Ohio 44139 USA (See Att	achment A)
MANAGORY OF FT	TINGS TO BE REGISTERS	D. CIRCLE ONE CATEGORY ONLY	ITIDE OF THE STANDARD OF CONSTRUCTS
C Valves: all line valves Valves: all line valves Expansion joints, flexible of Strainers, filters, separator Measuring devices, includis pressure transmitters Certified capacity-raind prebollers, pressure vessels, in Pressure retaining componing to the pressure retaining componing transmitters.	connections, and hose assem s, and steam traps ng pressure gauges, level ga assure reflef devices accepta piping and fusible plugs sents that do not fall into one	suges, sight glasses, levels, or ble as primary over pressure protection on	Rubber Products Manufacturers (ARPM) Hose Handbook
SHOW MANUFACTURERS N	AME, TRADEMARK, OR LO	OGO AS IT WILL APPEAR ON THE PRODUCT	TYPE OF CONSTRUCTION
Swa	agelok		FORGEO D WELDED O WINDURHT D CAST D OTHER X CRECKIBE OTHER PTFE Core
LIST OF SUPPORTING DOC	UNENTATION AND IDENT	FICATION OF THE ACTUAL ITEMS TO BE RE	GISTERED:
emperature ratings, and ide nanufacture of these fittings or in part and has been verif	of the end product do solve product for which register interfacetion markings are it is is regulated by a Quality fied by BSI believing it to be true, and	ed by Swagelok Company and bei emrity declare that the Information contains tretion is sought. The dimensions, material accordance with the herein named stands control Program which extends to each picture as being suitable for the discovering that it is of the same force and ef	s of construction, pressure ards. I further declare that the ant where fabrication occurs in who
Declared before me at U	al due to CO	notary signature of is VID-19 situation	fect as if made under oath.
ignature of Declarer: Declared before me at U his day of second controls longer of Controls	September 17 (Affix Official seal to the rig	notary signature of is VID-19 situation Office 2020	fect as if made under oath.
declared before me at U his day of second solutions of Oaths r Notary Public: (sign)	September 17 (Affix Official seal to the rig This	notary signature of is VID-19 situation OFFI , 2020 pht) s space for Regulatory Authority use	SPACE FOR THE
ignature of Declarer: declared before me at his day of second or Notary Public: (sign) Thi	September 17 (Affix Official seal to the rig This	notary signature of is VID-19 situation Office 2020	SPACE FOR THE
ignature of Declarer: declared before me at U his day of second commissioner of Oaths r Notary Public: (sign) Thi CRN: OD22736.5	September 17 (Affix Official seal to the rig This	notary signature of is VID-19 situation OFFI 2020 pht) space for Regulatory Authority use ralidated after ten (10) years from the date of	SPACE FOR THE CIAL SEAL Redection AVUT Boilers and
ignature of Declarer: lectared before me at U his day of second price of Oaths r Notary Public: (sign) Thi CRN: OD22736.5 FID#: 1214	September 17. (Affix Official seal to the rights registration must be rev	notary signature of is VID-19 situation OFFI , 2020 pht) space for Regulatory Authority use railidated after ten (10) years from the date of Nunavut	SPACE FOR THE CIAL SEAL
commissioner of Oaths r Notary Public: (sign) CRN:OD22736.5 FIO#:1214 Crimped Swagelok	CT series PTFE h	notary signature of is VID-19 situation OFFI 2020 oht) space for Regulatory Authority use alidated after ten (10) years from the date of Nunavut Nunavut REG	SPACE FOR THE CIAL SEAL Policy and Pressure Vessels Act
cignature of Declarer: Declared before me at U this day of second solution of Oaths on Notary Public: (sign) Thi CRN: OD22736.5 FIDM: 1214 Crimped Swagelok REGEMBLIES. 1/2" to 1. All fittings shall be registered. 2. Each category shall be sup	CT series PTFE h 2" sizes. ed in the name of the Manufapported with two Statutory De	notary signature of is VID-19 situation OFFI 2020 pht) space for Regulatory Authority use ralidated after ten (10) years from the date of Nunavut Nunavut REG	SPACE FOR THE CIAL SEAL Policy and Pressure Vessels Act
commissioner of Oaths r Notary Public: (sign) This day of section of Oaths r Notary Public: (sign) Thi CRN:OD22736.5	CT series PTFE h 2" sizes. ed in the name of the Manufaported with two Statutory Detring documentation. ade by the person having full the end product.	notary signature of is VID-19 situation OFFI 2020 pht) space for Regulatory Authority use ralidated after ter (10) years from the date of Nunavut Nunavut CRN OD 22 authority and Date NOVEM	SPACE FOR THE CIAL SEAL Pressure Vessels Act ISTERED

Territorial Registration Fee



Canadian Registration Number Submittal Category D Crimped Swagelok CT Series PTFE Hose

THIS IS PART OF CRN 0D22736.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

September 1, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok CT Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (CT series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

СТ			Pressure			
Series Hose Size	At Minimum Temp.	Room temperature (0°-100°F)	At Maximum Temp.	Retaining Material	End Connections and Sizes	Design Code of Construction
1/2"	1500 psig @ -65°F	1500 psig	1500 psig @ 450°F		Swagelok Tube Fitting [SL SM] 1/8" – 2" (3-50mm)	
3/4"	1100 psig @ -65°F	1110 psig	900 psig @ 450°F	Core Helical Convoluted PTFE	Male & Female NPT Tapered Pipe Fitting [PM PF] 1/8" – 2" Female & Male VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	
1"	750 psig @ -65°F	750 psig	490 psig @ 450°F	Braid 304 SS Braid Reinforcement End Connections	Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN AS] 1/4" – 2"	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
1 1/2"	675 psig @ -20°F	700 psig	330 psig @340°F	316 SS Crimp on Collar 300 series SS	Tube Butt Welds [TB] 1/2" – 1" Female & Male VCR Metal Gasket Face Seal [RF, RM] 1/8" – 2" Female ISO/BSP Parallel	
2"	525 psig @ -20°F	525 psig	485 psig @340°F		Threads (ISO 228) [FS] 1/4" – 1"	



Canadian Registration Number Submittal
Category D Crimped Swagelok CT Series PTFE Hose

THIS IS PART OF CRN
0D22736.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program


September 1, 2020 Page 2 of 2

Product Description

Swagelok's CT series hose is helical convoluted PTFE, 300 series stainless steel braided hose. All CT series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Perma tag (JT only)- Polyester tag encapsulated in platinum-cured silicone with customerspecified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN

0D22736.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man