



Technical Standards and Safety Authority  
 345 Carlingview Drive  
 Toronto, Ontario M9W 6N9  
 www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below

Swagelok

## STATUTORY DECLARATION Registration of Fittings

I, Joel Feldman, Vice President of Engineering  
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Swagelok Company  
(Name of Manufacturer)

Located at 29500 Solon Road, Solon, Ohio 44139 USA (Plant Address) (440) 248-4600 (Telephone No.) (440) 349-5970 (Fax No.)

do solemnly declare that the fittings listed hereunder, which are subject to the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, comply with all of the requirements of ASME B31.1 for unlisted components, and ASME B31.3 for unlisted components  
(Title of recognized North American Standard)  
 which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with \_\_\_\_\_ as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2015 which has been verified by the following authority, BSI

The items covered by this declaration, for which I seek registration, are category A. Fitting type fittings. In support of this application, the following information and/or test data are attached as follows:  
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents  
(drawings, calculations, test reports, etc.)

Declared before me at Solon in the state of Ohio  
 the 3rd day of October AD 2019.

Commissioner for Oaths:

Brenda Hammel  
(Printed name)  
Brenda Hammel  
(Signature)

Joel C. Feldman  
(Signature of Declarer)

### FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category A

CRN: OA22212.5

Registered by: [Signature]

Dated: Feb 29, 2020

NOTE: This registration expires on: March 1, 2030

**Technical Standards and Safety Authority**      **Boilers and Pressure Vessels Safety Program**  
**OFFICE REGISTERED**  
 C.R.N.: OA22212.5  
 Signed: [Signature]  
 Date: Feb 29, 2020

*\*Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.*

*Scope of registration: See attachment A and B attached [Signature]*

## Attachment B. Scope of Registration for Swagelok Titanium, Grade 4 (ASTM B348, B381) Tube Fittings (Category A)

This document represents the scope of Swagelok Titanium Tube Fittings covered by this submission for CRN approval. These Swagelok Tube Fittings have been evaluated in accordance with ASME B31.3 for unlisted components and ASME B31.1 for unlisted components.

### Summary Table

Product Description or Series	Material (Standard)	Port Connections and Sizes	Maximum Allowable Working Pressure		Design Code of Construction
			Up to 100°F	At maximum temperature	
Gaugeable Tube Fittings and Adapter Fittings	Titanium Grade 4 (ASTM B348/ASTM B381)	Swagelok End Connection 1/4 inch - 1/2 inch 6mm, 10mm, 12mm	See Table below	See Table below	ASME B31.3 (Unlisted Components)
		NPT Male 1/16 - 1 inch	8800 - 4200 psig	3520 - 1680 psig @ 600°F (315°C)	ASME B31.1 (Unlisted Components)
		NPT Female 1/16 - 1 inch	5300 - 3500 psig	2120 - 1400 psig @ 600°F (315°C)	ASME B31.1 (Unlisted Components)


### Titanium Swagelok Tube Fitting Pressure Rating Table

Swagelok End Connection Size	ASME B31.1 Maximum Allowable Working Pressures		ASME B31.3 Maximum Allowable Working Pressures	
	Up to 100°F	At maximum temperature 600°F (315°C)	Up to 100°F	At maximum temperature 600°F (315°C)
1/4 inch	7735 psig	3480 psig	9100 psig	4095 psig
3/8 inch	4930 psig	2218 psig	5800 psig	2610 psig
1/2 inch	3570 psig	1606 psig	4200 psig	1890 psig
6 mm	510 bar	229 psig	600 bar	270 psig
10 mm	289 bar	130 psig	340 bar	153 psig
12 mm	238 bar	107 psig	280 bar	126 psig




## Product Description

Swagelok Fittings are furnished in a variety of configurations and shapes (straight, elbow, tee or cross). Swagelok Fittings consist of at least one Swagelok End – a proprietary two-ferrule mechanical-grip design. The table below, as well as the “Configurations” section, covers a variety of other end connections.




## Configurations

### 1. Unions.



### 2. Male and Female connectors / adapters.



NPT Male Connectors

Female Connectors

THIS IS PART OF  
GRN 00222/2.5  
Technical Standard & Reference Library  
Boilers & Pressure Vessels  
Safety-critical

## Product Options:

Some of the product options listed below affect the pressure-temperature ratings in the "Scope of Registration" section above, but in all cases the pressure ratings are the same or less than those shown in the table on page 1.

- Sealant for NPT pipe threads:
  - Curable resin with PTFE
  - PTFE tape
- Bored through fittings
- Plastic ferrules, (Nylon, Teflon, PEEK)

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- Special marking
- Special cleaning
- Wire drills
- bulkhead configurations
- Snubbers/frits and orifice plates

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.

## Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

## References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

- Gaugeable Tube Fittings and Adapter Fittings MS-01-140, Rev Y
- Swagelok Tubing Data Sheet MS-01-107, Rev N



**Attachment A. Swagelok Manufacturing Locations**

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Company A.G. (European Technology Center) St. GallerstraBe 84 Lachen, Switzerland 8853 Switzerland
Swagelok Limited Tromode IM4 4RA Isle of Man	

