

Statutory Declaration Registration of Fittings

(a)	Design Qualification							
11	Joel Feldman							
3	Vice President, Engineering							
-	(Position eg, president, pla	ant manager, chief eng.)						
Of	Swagelok Company							
Control of the Contro	(name of c	ompany)						
Loca	ted at Headquarters: 29500 Solon Road, Solon, Oh (plant ac		Attachment A)					
do so	olemnly declare <mark>t</mark> hat the fittings listed her <mark>eunder, w</mark> hich are subje	ect to the Boilers & Press	sure Vessels Act:					
Or	required:							
X	are not covered by the provisions of the ANSI/ASME codes, a	and are therefore construe best current engineering	ucted to comply with ARPM Hose Handbooking practice, as shown by the supporting test					
	data	- M						
The	fittings ² covered by th <mark>is</mark> declaration, for whi <mark>ch I</mark> seek registration,	are	Category D. Hose					
	pport of the application, the following information, calculations ar O 9001:2015 Certificate, Attachment A, Attachment							
Decl	ared before me at	_						
In the		_						
115 115 115	Unable to get a notary signature		11211					
(or seal due to COVID-19 situation	no	1 tell					
	September 17, 2020		Signature of Declarer ³					
	For Official	Use Only						
	e application is accepted for registration in Category A Standard B51.	in accordance with	the Boilers and Prossure Vessels Act and					
Th	is registration must be revalidated after ten (10) years from the d	late of acceptance.	thregistré au Québa					
Re	gistered Number CRN	For the Chief Inspe	Régie du bâtiment Québec * *					
	-	- Allerton	T _C 11/12/2020					

2 All fittings are required to be registered in the name of the Manufacturer.

onciliation Three completed copied of Statutory Declaration form together with three copies of Catalogs, draabove fittings shall be submitted.

This form shall be completed and signed by the president of highest official in the manufacturing plan where the fitting is produced.



Canadian Registration Number Submittal
Category D Crimped Swagelok CT Series PTFE Hose

Attachment B: Scope of Registration for Crimped Swagelok CT Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (CT series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

СТ	Maximum Pressure		Pressure			
Series Hose Size	At Minimum Temp.	Room temperature (0°-100°F)	At Maximum Temp.	Retaining Material	End Connections and Sizes	Design Code of Construction
1/2"	1500 psig @ -65°F	1500 psig	1500 psig @ 450°F		Swagelok Tube Fitting [SL SM] 1/8" – 2" (3-50mm)	
3/4"	1100 psig @ -65°F	1110 psig	900 psig @ 450°F	<u>Core</u> Helical Convoluted PTFE	Male & Female NPT Tapered Pipe Fitting [PM PF] 1/8" – 2" Female & Male VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	
1"	750 psig @ -65°F	750 psig	490 psig @ 450°F	Braid 304 SS Braid Reinforcement End Connections	Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN AS] 1/4" – 2"	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
1 1/2"	675 psig @ -20°F	700 psig	330 psig @340°F	316 SS Crimp on Collar 300 series SS	Tube Butt Welds [TB] 1/2" – 1" Female & Male VCR Metal Gasket Face Seal [RF, RM] 1/8" – 2" Female ISO/BSP Parallel	
2"	525 psig @ -20°F	525 psig	485 psig @340°F	Threads (ISO 228) [FS] 1/4" – 1" Régie du bâtiment		





Canadian Registration Number Submittal
Category D Crimped Swagelok CT Series PTFE Hose


September 1, 2020 Page 2 of 2

Product Description

Swagelok's CT series hose is helical convoluted PTFE, 300 series stainless steel braided hose. All CT series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Perma tag (JT only)- Polyester tag encapsulated in platinum-cured silicone with customerspecified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man Swagelok Limited Utieglistré au Queile OD22736.56 Régie du bâtiment Québec

