UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME:	Swagelok Company		errette e e e e e e e e e e e e e e e e
MANUFACTURERS ADDRESS		l, Solon, Ohio 44139 USA	
PLANY LOCATIONS: Headou	arters: 29500 Solon	Road, Solon, Ohio 44139 USA (See A	ttachment A).
CATEGORY OF FITT	NGS TO BE REGISTER	ED. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
A Pipe fittings, including coupling Flanges: all flanges C Valves: all line valves D Expansion joints, flexible cont Strainers, filters, separators, of Measuring devices, including pressure transmitters C certified capacity-rated pressure boilers, pressure vessels, pip H Pressure-retaining companion	gs, tees, elbows, Ys, plug nections, and hose assen and steam traps pressure gauges, level gr ure relief devices accepta ing and fusible plugs to that do not fall into one	gs, unions, pipe caps, or reducers nblies: all types suges, sight glasses, levels, or sble as primary over pressure protection on	Association of Rubber Products Manufacturers (ARPM) Hose Handbook
Swa	aelok gelok	OGO AS IT WILL APPEAR ON THE PRODUC	I TYPE OF CONSTRUCTION FORGED CONVENTION CASY COTHER N ORECRUSS OTHER CARDON black- filled virgin PTFE core
LIST OF SUPPORTING DOCUM	MENTATION AND IDENT	TRICATION OF THE ACTUAL ITEMS TO BE	PECIETEDEO
my knowledge represents the temperature ratings, and ident manufacture of these littings it or in part and has been verifie	the end product do so product for which regis ification markings are is regulated by a Quality d by. BSI	termity declare that the information contain stration is sought. The dimensions, materi in accordance with the herein named stan- y Control Program which extends to each	als of construction, pressure dards. I further declare that the plant where fabrication occurs in whole that purpose and I make this solomo
	111.31		away as a taken ploet deal.
Signature of Declarer: Declared before me at This day of Commissioner of CathsOT & or Notary Public: (sign)		notary signature OFF	S SPACE FOR THE
	Thi	is space for Regulatory Authority use validated after ten (10) years from the date	of acceptance.
CRN: 0D22658.5 FID#: 1214 NC series PTFE hose as: 720psi (1/2") 375psi (3/4" Notes: 1. All fittings shall be registered 2: Each category shall be supportions and one copy of supportin 3. The declaration shall be mad responsibility for the quality of the 4. Quality control programs shall) @ -65F to 100F; in the name of the Manuf orted with two Statutory D g documentation, a by the person having fu e end product.	450F DT (acturer. leclaration DATE: Orf 5 d	E EDWARD ISLAND & ENVIRONMENT 58.59 2020
et a maximum interval of five (5) CRN expires Aug.31	years.	BOILER/PRESSURE	



Canadian Registration Number Submittal
Category D Crimped Swagelok NC series PTFE Hose

THIS IS PART OF CRN
0D22658.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

June 22, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok NC series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (NC series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

NC	Maximum Pressure (psig)					
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
3/8"	1250	1250	140	<u>Core</u> Convoluted Bore Carbon Black- filled (PTFE)	Swagelok Tube Fitting [SL SM] 1/8" – 2" (3-50mm) Male & Female NPT Tapered Pipe Fitting [PM PF] 1/8" – 2" Male and Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT FT]	
1/2"	720	750	130	Covered By Ceramic Insulating Wrap Braid Aramid Fiber Braid Reinforcement	1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2" Tube Butt Welds [TB] 1/2" – 1" Female & Male VCO O-ring Face seal Fitting [VF, VM]	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
3/4"	375	375	80	Connections 316 SS Crimp on Collar 300 series SS	1/8" - 2" Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8" - 2" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4"- 1"	

Product Description

NC series is standard Swagelok virgin Convoluted PTFE-lined hose with a Nomex insulating wrap and fiber braid reinforcement. All NC series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).



Canadian Registration Number Submittal Category D Crimped Swagelok NC series PTFE Hose


THIS IS PART OF CRN 0D22658.5

Technical Standards and Safety Authority Boilers and Pressure Vessels Safety **Program**

June 22, 2020 Page 2 of 2

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN 0D22658.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Safety

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	