

Technical Safety Authority of Saskatchewan

REGISTERED



CRN: CSA-0A21361.56

Registration Process administered by CSA Group per CSA B51

PH: (306) 798-7112

FAX: (306) 787-9273

Email:

2202 2nd Ave.
Regina, SK S4R 1K3
Toll Free: (866) 530-8599
Toll Free: (866) 760-9255
boilerpermits@tsask.ca
Website: www.tsask.ca

Statutory Declaration (Registration of Fittings)

TSK-1008

I. Declaration Information

I, Joel Feldman
Vice President, Engineering
(company title, e.g. vice president, plant manager, chief engineer)
(must be in a position of authority in the manufacturing plant where the fitting is produced)

In this space, show facsimile of manufacturer's logo or trademark as it will appear on the fitting.



of: Swagelok Company
(name of manufacturer)

located at: Headquarters: 29500 Solon Road Solon, Ohio 44139 USA
(Plant Address - Apt/Street) (City, Prov) (Postal Code)

do solemnly declare that the fittings listed hereinunder, which are subject to the **Saskatchewan Boiler and Pressure Vessel Safety Act** (check one)

Comply with the requirements of ASME B31.1 and ASME B31.3 which specifies the dimensions,
(title of recognized North American Standard)
Materials of construction, pressure / temperature ratings and identification marking of the fittings, or

Are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with _____ as supported by the attached data which identifies the dimensions, materials of construction, pressure / temperature ratings and the basis for such ratings, and the marking of the fittings for identification.

I further declare that the manufacturer of these fittings is controlled by a quality control program which has been verified by the following authority, BSI as being suitable for the manufacturer of these fittings to the stated standard. The fittings covered by this declaration, for which I seek registration, are Category A, Fitting

In support of this application, the following information, calculations and / or test data are attached:

ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents

II. Declaration

DECLARED before me at Solon In the State of Ohio
this 14th day of March, 2019

Brenda Hammel
(print name) Joel C. Felt
(Signature)
Brenda Hammel
(Signature of Commissioner of Oaths)

III. Office Use Only

To the best of my knowledge and belief, the application meets the requirements of the **Boiler and Pressure Vessel Safety Act** and **CSA B51, Clause 4.2**, and is accepted for registration in Category A

CSA-0A21361-56 Jun. 10. 2019 May. 1. 2029
(Registration Number) (Date Registered - MM DD YYYY) (Expiry Date - MM DD YYYY)
A. BANWATT
(For the Administrator / Chief Inspector)




TSK-1008
Rev. 10/2012
Page 1 of 1

*Note: See the attachment for the scope of the registration.

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man



STAMP OF
0A21361.56
Authority

Attachment B: Scope for Swagelok QC, QF, QM and QTM Series Quick-Connects (Category A)


This document represents the scope of the QC, QF, QM, and QTM Series Quick-Connects covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME B31.3-2016 for unlisted components.

0A21361.5

Summary Table

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		Design Code of Construction
				At -50 to 100°F	At maximum temperature	
QC4	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4" Male ISO 1/4"	3000 psi	500 psi @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
QC6	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 3/8", 10MM Female NPT 1/4", 3/8" Female ISO 3/8" Male NPT 1/4", 3/8" Male ISO 3/8"	1500 psi	400 psi @ 400°F	
QC8	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/2" Female ISO 1/2" Male NPT 1/2" Male ISO 1/2"	750 psi	300 psi @ 400°F	
QC4	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4" Male ISO 1/4"	2000 psi	300 psi @ 250°F	
QC6	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 3/8", 10MM Female NPT 1/4", 3/8" Female ISO 1/4", 3/8" Male NPT 1/4", 3/8" Male ISO 1/4", 3/8"	1000 psi	300 psi @ 250°F	
QC8	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/2" Female ISO 1/2" Male NPT 1/2" Male NPT 1/2"	500 psi	300 psi @ 250°F	

3076


ATTACHMENT TO
CRN: CSA-0A21361.56
Signed: [Signature]
178 Rexdale Boulevard, Toronto, ON Canada M9W 1R3


Swagelok

Canadian Registration Number Submittal #QC-2019
 Category A: Swagelok Quick Connects

Date March 14, 2019
 Page 2 of 4

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Temperature		Design Code of Construction
				At -50 to 100°F	At maximum temperature	
QF4, QF8	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/4", 3/8", 1/2", 6MM Female NPT 1/4", Female ISO Tapered 1/4" Female ISO Parallel 1/4"	6000 psi	400 psi @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
			Female NPT 3/8"	5300 psi	400 psi @ 400°F	
			Female NPT 1/2" Female ISO Tapered 1/2" Female ISO Parallel 1/2"	4900 psi	400 psi @ 400°F	
QF12, QF16	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 3/4", 1" Female NPT 3/4", 1"	4000 psi	200 psi @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
QF4	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/4"	3500 psi	300 psi @ 250°F	
			Swagelok Tube Fitting 6MM	3190 psi	300 psi @ 250°F	
			Swagelok Tube Fitting 3/8"	2200 psi	300 psi @ 250°F	
			Female NPT 1/4" Female ISO Tapered 1/4" Female ISO Parallel 1/4"	3300 psi	300 psi @ 250°F	
			Female NPT 3/8"	2400 psi	300 psi @ 250°F	
QF8	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 3/8"	2200 psi	300 psi @ 250°F	
			Swagelok Tube Fitting 1/2"	2100 psi	300 psi @ 250°F	
			Female NPT 3/8"	2600 psi	300 psi @ 250°F	
			Female NPT 1/2" Female ISO Tapered 1/2" Female ISO Parallel 1/2"	2400 psi	300 psi @ 250°F	
QF12, QF16	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 3/4"	1800 psi	200 psi @ 250°F	
			Swagelok Tube Fitting 1"	1500 psi	200 psi @ 250°F	
			Female NPT 3/4", 1"	2000 psi	200 psi @ 250°F	
QM2	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/16", 1/8" Female NPT 1/16", 1/8" Male NPT 1/16", 1/8"	4000 psi	200 psi @ 400°F	
QM2	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/16", 1/8" Female NPT 1/16", 1/8" Male NPT 1/16", 1/8"	2000 psi	200 psi @ 250°F	

40F6



ATTACHMENT TO
 C.R.N. CSA-CA-236000
 Signed: [Signature]
 178 Rexdale Boulevard, Toronto, ON Canada M9W 1R3

QA-21361 ✓
 Energy Authority
 Pressure Vessels
 Program

Swagelok


Canadian Registration Number Submittal #QC-2019
 Category A: Swagelok Quick Connects

Date March 14, 2019
 Page 3 of 4

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Temperature		Design Code of Construction
				At -50 to 100°F	At maximum temperature	
QTM2	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/4", 3/8", 6MM, 8MM Male NPT 1/4", 3/8" Female NPT 1/8", 1/4", 3/8" Female ISO Tapered 1/4" Female ISO Parallel 1/8", 1/4"	4500 psi	4500 psi @ 120°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
QTM4, QTM8	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/4", 3/8", 1/2", 3/4", 1", 6MM, 10MM, 12MM Male NPT 1/4", 3/8", 1/2", 3/4", 1" Female ISO Tapered 1/4", 1/2" Female ISO Parallel 1/4", 1/2" JIC 37° flare 1/4", 1/2"	3200 psi	3200 psi @ 120°F	
QTM2	Body	Alloy 400 (ASTM B164)	Swagelok Tube Fitting 1/4", 3/8", 6MM, 8MM Male NPT 1/4", 3/8" Female NPT 1/8", 1/4", 3/8" Female ISO Tapered 1/4" Female ISO Parallel 1/8", 1/4"	3200 psi	3200 psi @ 120°F	

Product Illustration

OA 21361.5



Product Options:

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be optional lubricants.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- QC, QF, QM, and QTM Series Quick-Connects Catalog MS-01-138, Rev S



0A-21361.5