NEW BRUNSWICK NUNAVUT NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY TITLE OF THE STANDARD OF CONSTRUCTION A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers **ASME B31.3** B Flanges: all flanges C Valves: all line valves D Expansion joints, flexible connections, and hose assemblies: all types Strainers, filters, separators, and steam traps Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certifled capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION FORGED | WELDED | WAGUGHT M DESCRIBE OTHER LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED; ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents DECLARATION: | Joel Feldman, Vice President, Engineering (see note 3) employed by_ Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards, I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath. 3/25/2021 | 10:45 AM EDT Signature of Declarer: Declared before me at Unable to get a notary USETHIS SPACE FOR THE day of signature or Seal due to OFFICIAL SEAL Commissioner of Oaths or Notary Public: (sign) COVID-19 situation (Affix Official seal to the right) This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of acceptance. Notes: 1. All fittings shall be registered in the name of the Manufacturer. 0F21398.2Y 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and 05/03/2021 responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.



Canadian Registration Number Submittal
Category F: Swagelok M1, M2 Variable Area Flow Meters

March 24, 2021 Page 1 of 2

Attachment B. Scope of Registration for Swagelok M1, M2 Model Variable Area Flow Meters (Category F)

Product Scope

This document represents the scope of Swagelok's M1 and M2 model Variable Area Flowmeters covered by this CRN approval. These flowmeters have been evaluated in accordance with appropriate North American standards. See the table below for specific design codes of construction for each product series.

Product Description



ABSA SAFETY CODES ACT - PROVINCE OF ALBERTA ACCEPTED: 0F21398.2 See acceptance letter for conditions of registration. Date: 2021-04-14 By: East Passary For ZANA RADISAVLJEVIC. P. Tech. (Eng.)

This stamp and signature have been affixed electronically to this registered design as required by Section 20(1) of the Pressure Equipment Safety Regulation, in accordance with the Electronic Transactions Act.

Summary Table


Model	Material	Port Connections and Sizes	Max. Inlet Pressure at 70° F (psig)	Min. Temperature Rating (°F)	Max. Temperature Rating (°F)	Design Code of Construction
VAF-M1	316L SS	NPT 1/4"	1885	-4	302	ASME B31.3
VAF-M2	316L SS	NPT 1/4"	1885	-4	302	ASME B31.3



Canadian Registration Number Submittal
Category F: Swagelok M1, M2 Variable Area Flow Meters

March 24, 2021 Page 2 of 2

Sample Drawings with Nominal Dimensions



Product Options:

Additional options and non-pressure boundary alterations that do not affect the pressuretemperature ratings may be made available within the scope of this approval. Examples of these include the following:

- Gasket or O-ring materials
- Limit switches
- Top-mounted needle valve
- Silconert coating
- Special cleaning
- Electronic (LED) display

Quality System

The Swagelok Company quality system complies with the requirements of EN ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

Variable Area Flowmeters, G Series and M Series, Product Catalog MS-02-346 Rev. H

Canadian Registration Number Submittal Page 1 of 1

Attachment A. Manufacturing Locations

This document lists the location where end item manufacturing activities take place.

Krohne Messtechnik GmbH Ludwig-Krohne-Str. 5 47058 Duisburg Germany

Notes:

1. All fittings shall be registered in the name of the Manufacturer.

2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.

3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.

4. Quality control programs shall be resubmitted for validation

at a maximum interval of five (5) years.



Canadian Registration Number Submittal
Category F: Swagelok M4, M4H Variable Area Flowmeters


March 24, 2021 Page 1 of 2

Attachment B. Scope of Registration for Swagelok M4, M4H Model Variable Area Flowmeters (Category F)

Product Scope

This document represents the scope of Swagelok's M4 and M4H model Variable Area Flowmeters covered by this CRN approval. These flowmeters have been evaluated in accordance with appropriate North American standards. See the table below for specific design codes of construction for each product series.

Product Description



THIS IS PART OF CRN 0F23192.5


Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Summary Table


Model	Material	Port Connections and Sizes	Max. Inlet Pressure at 70° F (psig)	Min. Temperature Rating (°F)	Max. Temperature Rating (°F)	Design Code of Construction
VAF-M4 (1/2 inch dia. Tube)	316L SS	NPT 1/2", 3/4" ASME flange 1/2", 3/4", 1"	2888	-40	572	ASME Section VIII Division 1, ASME B31.1, ASME B31.3
VAF-M4 (1 inch dia. Tube)	316L SS	NPT 3/4", 1" ASME flange 3/4", 1"	1393	-40	572	ASME Section VIII Division 1; ASME B31.1; ASME B31.3
VAF-M4H (1/2 inch dia. Tube)	316L SS	NPT 3/4" ASME flange 1/2", 3/4", 1"	2888	-40	572	ASME Section VIII Division 1; ASME B31.1; ASME B31.3
VAF-M4H (1 inch dia. Tube)	316L SS	NPT 1-1/4" ASME flange 1"	1393	-40	572	ASME Section VIII Division 1; ASME B31.1; ASME B31.3





Canadian Registration Number Submittal Category F: Swagelok M4, M4H Variable Area Flowmeters

Sample Drawings with Nominal Dimensions



Product Options:

Additional options and non-pressure boundary alterations that do not affect the pressuretemperature ratings may be made available within the scope of this approval. Examples of these include the following:

- Gasket or O-ring materials
- Limit switches
- Top-mounted needle valve
- Silconert coating
- Special cleaning
- Electronic (LED) display

THIS IS PART OF CRN

0F23192.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Quality System

The Swagelok Company quality system complies with the requirements of EN ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

• Variable Area Flowmeters, G Series and M Series, Product Catalog MS-02-346 Rev. H

Attachment A. Manufacturing Locations

This document lists the location where end item manufacturing activities take place.

Krohne Messtechnik GmbH Ludwig-Krohne-Str. 5 47058 Duisburg Germany

THIS IS PART OF CRN

0F23192.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program