NEW BRUNSWICK NUNAVUT

NOVA SCOTIA YUKON

PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NA	ME: Swagelok Company	
MANUFACTURERS AD		
PLANT LOCATIONS:	Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Atta	achment A)
CATEGORY	OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
B Flanges: all flanges C Valves: all fine valve: D Expansion joints, flex E Strainers, filters, sepa F Measuring devices, in pressure transmitters G Certified capacity-rate boilers, pressure ves H Pressure retaining co	ble connections, and hose assemblies: all types arators, and steam traps actuding pressure gauges, level gauges, sight plasses, levels, or	Rubber Products Manufacturers (ARPM) Hose Handbook
SHOW MANUFACTURE	RS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT	TYPE OF CONSTRUCTION
Sw	agelok	PORDED WELDED O WINDUGHT D CAST OTHER X DESCRIBE OTHER X Nylon and Polyethylene Core
LIST OF SUPPORTING	DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REC	SISTERED:
esponsibility for the quing knowledge represer emperature ratings, an nanufacture of these fi ir in part and has been	islify of the end product do solemnly declare that the information contained into the product for which registration is sought. The dimensions, materials it identification markings are in accordance with the herein named standar tings is regulated by a Quality Control Program which extends to each pla	of construction, pressure rds. I further declare that the ant where fabrication occurs in whole at purpose and I make this solemo
Signature of Declarer:	10/22/2020 10:20 AM EDT	
eclared before me at	Unable to get a notary signature on is	SPACE FOR THE
commissioner of Oath	of seal due to COVID-19-situation OFFI 5 - October 22, 2020 (Affix Official seal to the right)	CIAL SEAL
	This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of	faccontance
CRN: 0D22889.5		JENTON
FID#: 1214		
Nylon series (7) Notes:Polyethylen 1. All fittings shall be reg 2. Each category shall be forms and one copy of si 3. The declaration shall responsibility for the qua 4. Quality control progra at a maximum interval of	Ims shall be resubmitted for validation I five (5) years. e.c. 16th, 2030 - DG	
	Con	FOC RRANCH



THIS IS PART OF CRN
0D22889.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

September 21, 2020 Page 1 of 4

Attachment B: Scope of Registration for Swagelok Nylon Series (7N, 7R, 8N & 8R) and Polyethylene Series (7P) Hose Assemblies (Category D)

This document represents the scope of Swagelok Nylon Series (7N, 7R, 8N, 8R) and Polyethylene Series (7P) Hose Assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

Product Description or Series	Pressure retaining Material	End Connections and Sizes	Nominal Hose Size (in.)	Maximum Pressure at Temperature (psig)		Design Code
				At -40 to 70°F Temp.	At Maximum Temp. (200°F)	of Construction
7N Nylon Hose	Smooth Bore Core SAE nonconductive nylon (7N)	SM] 1/4" – 1/2" (6-12mm) Female 37° JIC with female swivel nut [AN, AS] 1/4" – 1/2" Male ISO/BSP Tapered (ISO 7) Pipe Threads [MT]	1/4	2750	1750	
	Synthetic fiber reinforcement Hose Cover		3/8	2250	1750	
	Polyurethane cover End Connections 316 SS	1/4" – 1/2" Male NPT Tapered Pipe Fitting [PM] 1/4" – 1/2"	1/2	2000	1750	
7R Nylon Hose	Smooth Bore Core Nylon (7R) Core Covered By Synthetic fiber reinforcement Hose Cover SM] 1/4" – 1/2" (Female 37° JI female swivel nut 1/4" – 1/2 Male ISO/BSP	Swagelok Tube Fitting [SL SM] 1/4" – 1/2" (6-12mm) Female 37° JIC with	1/4	1750	2000	- Association for
		1/4" – 1/2" Male ISO/BSP Tapered (ISO 7) Pipe Threads [MT]	3/8	2250	2000	Rubber Products Manufacturers (ARPM) Hose
	Polyurethane cover End Connections 316 SS	1/4" – 1/2" Male NPT Tapered Pipe Fitting [PM] 1/4" – 1/2"	1/2	2000	1500	` Handbook
8R Nylon Hose	Smooth Bore Core Nylon Blend Thermoplastic Core Covered By Synthetic fiber reinforcement Hose Cover Polyurethane cover	Swagelok Tube Fitting [SL SM] 1/4" – 1" (6-12mm)	1/4	5000	3250	
		Female 37° JIC with female swivel nut [AN, AS] 1/4" – 1" Male ISO/BSP Tapered (ISO 7) Pipe Threads [MT] 1/4" – 1"	3/8	4000	3250	
			1/2	3500	2750	
			3/4	2250	1500	
	End Connections 316 SS	Male NPT Tapered Pipe Fitting [PM] 1/4" – 1"	1	2000	1125	



THIS IS PART OF CRN

0D22889.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

September 21, 2020 Page 2 of 4

Product Description or Series	Pressure retaining Material	End Connections and Sizes	Nominal Hose Size (in.)	Maximum Pressure at Temperature (psig)		Design Code
				Up to 70°F Temp.	At Maximum Temp.	of Construction
8N Nylon Hose	Smooth Bore Core SAE nonconductive nylon Core Covered By Synthetic fiber reinforcement Hose Cover Polyurethane cover End Connections 316 SS	Swagelok Tube Fitting [SL] 3/4" Female 37° JIC with female swivel nut [AS] 3/4" Male ISO/BSP Tapered (ISO 7) Pipe Threads [MT] 3/4" Male NPT Tapered Pipe Fitting [PM] 3/4"	3/4	2250 @ -40°F to 70°F	1750 @ 200°F	Association
7P Polyethylene Hose	Smooth Bore Core	Female 37° JIC with female swivel nut [AS] 1/4" – 1" Male ISO/BSP Tapered (ISO 7) Pipe Threads [MT] 1/4" – 1"	1/4	2750 @ -10°F to 70°F	1500 @ 150°F	for Rubber Products Manufacturers
	Polyethylene Core Covered By		3/8	2250 @ -10°F to 70°F	2250 @ 150°F	(ARPM) Hose Handbook
	Synthetic fiber reinforcement Hose Cover		1/2	2000 @ -10°F to 70°F	1750 @ 150°F	
	Polyurethane cover End Connections		3/4	1250 @ -10°F to 70°F	900 @ 150°F	
	316 SS		1	1500 @ -10°F to 70°F	1200 @ 150°F	





THIS IS PART OF CRN 0D22889.5


Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

September 21, 2020 Page 3 of 4

Product Description









THIS IS PART OF CRN 0D22889.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

September 21, 2020 Page 4 of 4

Product Options:

Additional options and non-pressure boundary alterations that do not affect pressure ratings are within the scope of this approval. Examples of these options include but are not limited to:

- Spring guards (such as S Full length spring guard and S2 Short length spring guard)
- Sleeves (such as F Fire jacket sleeve with metallic tie lock bands; F1 Thermo sleeve with metallic tie lock bands)
- Tags and special markings
- Pipe Thread Sealants
- Special Testing

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180, Rev. U.

THIS IS PART OF CRN 0D22889.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man