# UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick Nunavut	Nova Scotia Yukon	Prince Edward Island Northwest Territories	Newfoundland and Labrador				
Manufacturers Na	me:Swagelok Company		and an				
	dress: 29500 Solon Road, S	Golon, Ohio 44139-3492					
		oad, Solon, Ohio 44139-3492 (See Attachm	nent A)				
Categor A Pipe fittings, includii B Flanges: all flanges C Valves: all line valve D Expansion joints, fle E Strainers, filters, sep F Measuring devices, transmitters G Certified capacity-ra boilers, pressure ves	y of Fittings to be regis ag couplings, tees, elbows, Y as xible connections, and hose parators, and steam traps including pressure gauges, I ted pressure relief devices a ssels, piping and fusible plug	tered. Circle one Category only 's, plugs, unions, pipe caps, or reducers assemblies: all types evel gauges, sight glasses, levels, or pressu cceptable as primary over pressure protecti	<u>Title of the Standard of</u> <u>Construction</u> British Standards Institution				
Show Manufacture	s: Class 1 Class 2 C rs Name, Trademark, or UGELOK	lass 3 □ , (Meeting CNSC or ASME require Logo as it will appear on the production	rements) <u> ct</u> <u> Type of Construction</u> Forged Welded Wrought Cast Other Describe other:				
		ntification of the actual Items to be re ertificate, Support Documents	registered: s: Attachment B, Catalog Informatic				

#### **Declaration:**

**Declaration:** I <u>Jay Nordholt</u>, Vice President, Engineering (see note 3) employed by <u>Swagelok Company</u> and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by <u>Bsi</u> as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: SNs: Stant	
Declared before me at	
This <u>At</u> day of <u>May</u> AD 2023	ELEANOR L DUKE
Commissioner of Oaths	State of Ohio
Or Notary Public: (sign)	A My Comm. Expires May 27, 2027
(Affix Official seal to the right)	
	ulatory Authority use.
This registration must be revalidated after CRN: 0C16304.5 Rev1	ten (10) years from the date of acceptance. NI OFA
FID#: 1214	BY TO
Notes:	
1. All Fittings shall be registered in the name of the Manufacturer.	CRN 0C16304.5Y REV1
2. Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.	
<ol> <li>The Declaration shall be made by the person having full authority and responsibility for the quality of the end product.</li> </ol>	DATE
4. Quality Control programs shell be resubmitted for validation. Scope: CRN renewal, K Series Pressure Regulators	OU Sect 0 - Filme Rev.2
(Jaci. KPR, KCY, KCM, KLF, KHF, KCP, KPP, KPF,	ERC ARA
KHP, KHŘ, KBP, KFB, KCB, KPB, KHB, KEV-Diaph., KEV-Piston, KSV), 15 plant locations.	and the second
ASME B31.1, B31.3 code of construction.	
CRN expires Aug. 15th. 2033 (DGallant)	

# Attachment B. Scope for Swagelok K Series Pressure Regulators (Category C)

#### Product Scope

This document represents the scope of the K Series Pressure Regulators covered by this submission for CRN approval. The Swagelok K Series Pressure Regulators were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

# Summary Table

	ure nt	Main Pressure Bearing		Maximum Rated Pressure				
Product Series Main Pressure Bearing Component	ו Press Bearing mpone		Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
	Material		Inlet	Outlet	Inlet	Outlet		
		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 ⁰F	500 psi @ 100 ⁰F	3600 psi @ 392 <sup>o</sup> F	500 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted
			Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	3600 psi @ 100 ⁰F	500 psi @ 100 ⁰F	3600 psi @ 392 ⁰F	500 psi @ 392 <sup>o</sup> F	
KPR	Body	Brass (UNS C67500 / ASTM A479)						Components) and ASME B31.3
		Alloy 400 (UNS N04400 / ASTM B164) Alloy C-276 (UNS N10276 / ASTM B574)	Female NPT 1/4"	3600 psi @ 100 ⁰F	500 psi @ 100 ºF	3600 psi @ 392 <sup>º</sup> F	500 psi @ 392 <sup>o</sup> F	(Unlisted Components)
KCY Body		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 <sup>º</sup> F	500 psi @ 100 <sup>º</sup> F	3600 psi @ 392 <sup>º</sup> F	500 psi @ 392 <sup>o</sup> F	
	Body	Brass (UNS C67500 / ASTM B138)		3600 psi @ 100 <sup>º</sup> F	500 psi @ 100 <sup>o</sup> F	3600 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
	Dody	Alloy 400 (UNS N04400 / ASTM B164)	(UNS N04400 Female NPT 1/4"					
		Alloy C-276 (UNS N10276 / ASTM B574)						
ксм	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 <sup>0</sup> F	500 psi @ 100 ⁰F	3600 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KLF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ⁰F	250 psi @ 100 ⁰F	3600 psi @ 392 <sup>o</sup> F	250 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure nt	Main		Maximum Rated Pressure				Design Code of Construction
Product Series	Series Bearing Bearing		Port Connections and Sizes	At ambient temperature		At maximum temperature		
	Mair E Co	Material		Inlet	Outlet	Inlet	Outlet	
KHF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	3600 psi @ 100 ⁰F	250 psi @ 100 ⁰F	3600 psi @ 392 ⁰F	250 psi @ 392 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСР	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	3600 psi @ 100 ⁰F	1500 psi @ 100 ⁰F	3600 psi @ 392 ⁰F	1500 psi @ 392 <sup>º</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КРР	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 ⁰F	3000 psi @ 100 ⁰F	6000 psi @ 392 ⁰F	2975 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KPF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	6000 psi @ 100 ⁰F	4000 psi @ 100 ⁰F	6000 psi @ 392 ⁰F	4000 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КНР	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ⁰F	8000 psi @ 100 ⁰F	10000 psi @ 392 ⁰F	8000 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KHR	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ⁰F	8000 psi @ 100 ⁰F	10000 psi @ 212 ⁰F	8000 psi @ 212 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КВР		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4" Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	500 psi @ 100 ⁰F	500 psi @ 100 ⁰F	500 psi @ 392 ⁰F	500 psi @ 392 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
	Body	Brass (UNS C67500 / ASTM B138) Alloy 400 (UNS N04400 / ASTM B164) Alloy C-276 (UNS N10276 / ASTM B574)	Female NPT 1/4"	500 psi @ 100 <sup>0</sup> F	500 psi @ 100 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and <u>ASME B31.3</u> (Unlisted Components)

	ure nt	Main		Maximum Rated Pressure				Design Code of Construction
Product Series Main Pressure Bearing Component		Main Pressure Bearing	Port Connections and Sizes	At ambient temperature		At maximum temperature		
	Mair E Co	Material		Inlet	Outlet	Inlet	Outlet	
KFB	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	250 psi @ 100 <sup>o</sup> F	250 psi @ 100 ºF	250 psi @ 392 ⁰F	250 psi @ 392 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	375 psi @ 100 ⁰F	375 psi @ 100 ⁰F	375 psi @ 392 ⁰F	375 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КРВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3000 psi @ 100 ºF	3000 psi @ 100 ºF	2975 psi @ 392 <sup>o</sup> F	2975 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КНВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	8000 psi @ 100 ºF	8000 psi @ 100 ºF	8000 psi @ 212 ⁰F	8000 psi @ 212 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (diaphr agm)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 <sup>o</sup> F	3600 psi @ 392 ⁰F	500 psi @ 392 ⁰F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (piston)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	3000 psi @ 100 <sup>o</sup> F	3600 psi @ 392 ⁰F	2975 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KSV	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ⁰F	500 psi @ 100 ⁰F	3600 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>o</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

## **Product Illustration**



# **Typical Product Characteristics**:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

PCTFE seat material PEEK seat material

Some of the product options listed below do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

ASTM G93 Level-E cleaned Swagelok SC-11 cleaned Handle Type (e.g. knob, thumbwheel, etc) Panel Mounting

#### Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The K Series Pressure Regulators are manufactured at a Swagelok Company locations in Solon, Ohio and Tromode, Isle of Man, British Isles.

## **References**

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

• K Series Pressure Regulator Catalog MS-02-230, Rev Q